BVS Series - Seacock/Strainer CombinationInstallation, Operation, and Maintenance

Installation: Thread the seacock portion onto an appropriately sized bronze thruhull fitting. You may need to cut down the length of the thru-hull so that it does not bottom out inside the seacock before proper compression of the hull and backing block has been achieved.

Use marine grade caulking between the seacock flange and the backing block, and between the thru-hull fitting flange and the hull.

Orient the seacock so as to provide un-obstructed access to the seacock handle, assuring that full 90-degree movement of the handle is possible. (To simplify plumbing hook-up the strainer head may be rotated in 90-degree increments after the seacock has been secured).

Bolt the seacock securely to the backing block with stainless steel bolts.

Connect the seacock to the boat's bonding system with 14-gauge wire and a ring connector. A bonding screw bolt is provided on the seacock flange for this purpose.

The BVS model number identifies the NPT pipe size that the strainer head is threaded (for example, BVS-750 means the strainer outlet is 3/4" NPT).

ITEM DADT NAME

Select a pipe-to-hose adaptor that matches the threaded strainer head and that also matches the hose size you will use to plumb the rest of the system. Full flow and standard flow, straight and 90-degree fittings are available. (See attached information sheet). Apply TFE thread tape to threaded NPT connections, and double-clamp all hose connections.

Seacock Operation: Rotate the handle to the mechanical stop in the vertical position to open the seacock. Rotate the handle to the mechanical stop in the horizontal position to close the seacock.

The square hole in the handle (after 011001) is for use with a ratchet handle, and is for the purpose of easing valve activation.

Strainer Operation: Unscrew the threaded strainer cap to inspect or service the filter basket. Although hand-tight is sufficient for a good O-ring seal, the cap has three (3) holes for the use of GROCO SW-2531 spanner wrench if additional tightening is desired, or if the cap is difficult to break loose after an extended time.

DVC 10E0

DVC 1EAA

Maintenance:

Inspect and clean the filter basket frequently. Apply silicon based of Teflon based waterproof grease to the strainer cap threads and O-ring to ease loosening the cap for the next inspection.

BVS is designed for in-field serviceability. If replacement of internal valve parts is ever required, the valve lock nut located at the bottom of the strainer (top of the valve) may be removable by first removing the set screws that prevent it from turning. Once the set screws have been removed, access to the valve ball and seats is possible.

Lubricate the threads and O-ring with silicon or Teflon grease before re-assembly.

The stem seals are accessible by removing the handle and unscrewing the brass nut. Pull the stem straight out for access to the stem seals.

	ITEM	PART NAME	QTY	BVS-750	BVS-1000	BVS-1250	BVS-1500
	1	Filter Basket, Stainless Steel	1	SSS-754	SSS-1004	SSS-1254	SSS-1504
		Filter Basket, Monel (optional)	1	SS-754	SS-1004	SS-1254	SS-1504
	2	Sight Glass	1	S-70-A	SVS-1006	SVS-1257	S-88
	• 3	Gasket	2	#9R	#8R	#8R	#10R
	• 4	O-Ring	1	2-144	2-151	2-151	2-238
	5	Cap Nut	4	1420CS	1420CS	1420CS	1420CS
	6	Lockwasher	4	14SS	14SS	14SS	14SS
WEGINAWOAE EADOLATONIES, INC. AEE MIGHTS NESENVED.	7	Strainer Top	1	SS-751	SS-1001	SS-1251	SS-1501
	8	Strainer Cap	1	SS-502-B	SS-1002-B	SS-1002-B	ARG-1501-B
	9	Tie Rod	4	S-73-C	SVS-1009	SVS-1259	S-73-B
	10	Valve Lock Nut	1	BVS-752	BVS-1002	BVS-1252	BVS-1502
	11	O-Ring	1	2-122	2-127	2-135	2-140
	12	Ball Seat	2	BV-756	BV-1006	BV-1256	BV-1506
	13	Ball	1	BV-754	BV-1004	BV-1254	BV-1504
	14	Valve Body	1	BVS-750-B	BVS-1000-B	BVS-1250-B	BVS-1500-B
	15	Drain Plug	2	1827HB	1827HB	1827HB	1827HB
	• 16	Driver Seal	2	1-015	1-017	1-017	1-116
	17	Driver	1	BVS-751-A	BVS-1001-A	BVS-1251-A	BVS-1501-A
	18	Driver Nut	1	BV-503-A	BV-1003-A	BV-1003-A	BV-1503-A
	19	Handle	1	BV-508	BV-1008	BV-1008	BV-1508
	20	Washer	1	14FS	14FS	14FS	38FS
	21	Lock Nut	1	1228X38HS	1420X12HS	1420X12HS	3816X15HS
				and 14SS	and 14SS	and 14SS	and 38SS
5	22	Сар	1	PFW-10	PFW-11	PFW-11	PFW-12
	•	Service Kit		BVS-1	BVS-2	BVS-2	BVS-3

OTV | DVC 7E0 | DVC 1000

